

## Vertiv™ Integrated Rack Solution

## Reference Design #34

### Essential Conditioned and Controlled 42U Rack 3000VA Capacity

#### Solution Requirements

##### Physical Protection

- Safeguard network gear from environmental threats and unauthorized access.
- Prevent dust, debris, and moisture from damaging equipment.

##### Power Protection

- Prevent business interruption caused by power loss or power fluctuations with battery backup technology.
- Achieve maximum uptime with redundant gear protecting critical application during an unexpected equipment failure.

##### On-Site Management

- Simplify deployment and support future growth with infrastructure designed for total compatibility and scalability.
- Recover business critical floor space with IT infrastructure designed with tight spaces in mind.
- Streamline deployment and get critical applications up and running faster with on-site services and support.

#### Form Factor: Rack

**Objective:** Support critical IT applications in environments designed specifically for IT equipment.

#### Recommended Environment

Climate-controlled physically secure environment with power, air conditioning and airflow management in place providing temperature and humidity optimization specifically designed for IT equipment.

- Converted Closet
- Server Closet
- Network Closet

#### Integrated Solution Summary

<b>Capacity</b>	3000VA/2700W
<b>Rack(s)</b>	42U x 600mm x 1100mm (HxWxD)
<b>Power Protection</b>	Line Interactive UPS
<b>Redundancy</b>	N
<b>Power Distribution</b>	rPDU, Basic Standard, 16A, 230V, 3.6kW, Vertical, (20) IEC C13, (4) IEC C19, C20, Black Powder Coat.
<b>Cooling</b>	Optional Upgrade
<b>Containment</b>	Optional Upgrade
<b>Monitoring</b>	Optional Upgrade
<b>Services</b>	Optional Upgrade
<b>Warranty</b>	3 years
<b>Software</b>	Optional Upgrade

## Integrated Solution Includes

Qty	Product Summary	SKU	Description
1	Rack	VR3100	VR3100ÿ- 42U x 600mm x 1100mm (HxWxD) Vertiv™ VR Rack
1	UPS	EDGE-3000IRT2UXL	Vertiv™ EDGE UPS 3000VA/2700W. Manageable and efficient line interactive UPS, with with controllable outlets and extended runtime options. Compact 2U rack mount design for Edge applications and offering up to 6 minutes of runtime when loaded to 100%.
1	Rack PDU	VP7552	rPDU, Basic Standard, 16A, 230V, 3.6kW, Vertical, (20) IEC C13, (4) IEC C19, C20, Black Powder Coat

\*Additional accessories and components are required and included in the integrated solution. Contact a Vertiv Partner for the complete bill of materials, to receive pricing, and to purchase.

## Recommended Upgrades

Qty	Product Summary	Model #:	Description
1	UPS COMM Card	IS-UNITY-SNMP	The interface card delivers SNMP, Telnet and web-management capability for enhanced communications and control of Liebert® UPS. The card manages a wide range of operating parameters, alarms and notifications, transmitting data over the network. Visit Vertiv.com for a free Vertiv™ Power Assist software download to gracefully shutdown an IT device when the UPS battery backup experiences a threatening condition.
1	IT Management	AV3108-001	Vertiv™ Avocent AV3000 Rackmount KVM Over IP Switch   CAC   8 Port KVM switches   Local and Remote Access (AV3108-001)
1	Warranty and Service	RUPS-WE1-005	1-year Extended Warranty - This extends standard warranty by one year. Covers electronic parts and batteries.
1	IT Management	ACS8008SAC-404	The Vertiv™ Avocent® ACS8000 Serial Console System delivers secure in-band and out-of-band visibility and control to downstream equipment in enterprise data centers, as well as cloud and colocation facilities. This serial console system serves as a secure management gateway and single point of entry keeping you connected to critical IT equipment even in the event of partial or total data center outages.

Explore all **Commercial and Office** form factors and power configurations available, **Endpoint, Rack, and Row** by visiting the Solution Builder on [Vertiv.com](https://www.vertiv.com) or by contacting a Vertiv Sales Representative.