

## Vertiv™ Integrated Rack Solution

## Reference Design #44

### Premier Conditioned and Controlled (4) 42U Rack 24kVA Capacity

#### Solution Requirements

##### Physical Protection

- Safeguard network gear from environmental threats and unauthorized access.
- Prevent dust, debris, and moisture from damaging equipment.

##### Power Protection

- Prevent business interruption caused by power loss or power fluctuations with battery backup technology.
- Achieve maximum uptime with redundant gear protecting critical application during an unexpected equipment failure.

##### On-Site Management

- Simplify deployment and support future growth with infrastructure designed for total compatibility and scalability.
- Recover business critical floor space with IT infrastructure designed with tight spaces in mind.
- Streamline deployment and get critical applications up and running faster with on-site services and support.

##### Remote Management

- Maintain peace of mind one or more remote sites are up and running with real-time notifications.
- Save time by remotely accessing and rebooting unresponsive network equipment without an on-site visit.

##### Site-Maintenance

- Ensure continuity of business with remote access and management of critical systems.
- Maximize your investment with on-site equipment maintenance and extended warranty protection.

##### Thermal Management

- Cool critical IT gear in high density or high temperature environments.

#### Form Factor: Row

**Objective:** Support critical IT applications in data center environments designed specifically for IT equipment.

#### Recommended Environment

Climate-controlled physically secure environment with power, air conditioning and airflow management in place providing temperature and humidity optimization specifically designed for IT equipment.

- Enterprise Data Center
- Managed Hosting Facility
- Colocation Data Center
- Cloud Data Center

#### Integrated Solution Summary

<b>Capacity</b>	36kVA/36kW
<b>Rack(s)</b>	Qty. 6 - 42U X 1200 X 800 (HxWxD)
<b>Power Protection</b>	Double Conversion Online
<b>Redundancy</b>	N+1 backup power, 2N rack power distribution, and N cooling
<b>Power Distribution</b>	48A Single Phase, 240V Max; 11.0kW 24A 3 Phase DELTA, 240V Max; 8.6kW 16A Three Phase WYE, 240/415V Max
<b>Cooling</b>	Included
<b>Containment</b>	Open
<b>Monitoring</b>	Included
<b>Services</b>	Included
<b>Warranty</b>	3 years
<b>Software</b>	Included

## Integrated Solution Includes

Qty	Product Summary	SKU	Description
4	Rack	VR3350	Vertiv™ VR Rack supports a wide variety of equipment, including servers, storage, switches, routers, PDUs, UPSs, console port servers and KVM switches. Dimensions 42U x 800mm x 1100mm (HxWxD).
7	Cable Management	VRA8571, VRA8561, VRA8571	The Vertiv VR Cable Trough System is a comprehensive line-up of accessories for the concealment and organization of power and communications cables. The NEMA standard rack cable tray system is available for 300 mm, 600 mm, and 800 mm wide, and includes enclosures, connectors, barriers, and grounding equipment.
1	UPS	ITA22C1D200A00	With true online double conversion technology, unity power factor and extremely compact rack / tower design, the Liebert ITA2 is the ideal power protection for computer rooms, storage and network devices.
8	Rack PDU	UU30009L	Vertiv™ Geist™ rPDU, Switched Outlet Level Monitoring EC, Variable Power Configuration, Vertical, (30) Locking IEC C13, (6) Locking IEC C19, Universal Inlet.
1	Row Based Air Cooling	CR035RA-11547620	CR035RA 600mm Wide CRV Unit with outdoor condensing unit and lee-temp kit.
2	IT Management	MPU2032DAC-001, ACS8032-EU-DAC	The Avocent MergePoint Unity MPU2032DAC-001 is a 32-port, 2 digital KVM path, with dual AC power supply. The MergePoint Unity switch includes both KVM over IP and Serial Console Management technology in a single appliance. This combination provides IT administrators a complete and secure, remote management solution to access and control servers, networking equipment and other devices found in data centers and branch offices.
2	Warranty and Service	PS-ACP-ST8X5-ITA20, ACP-WP1-8WH-8R8WH-12	Startup ITA2 10/15/20 kVA (8x5), Preferred Warranty 1YR-PM8x5-8HR RESP8x5 ITA2 10/15/20kVA
1	Software	DSV4.5-BASE, DSV4.5-500DEV, 1YRSLV-500DEV	DSView delivers secured web-browser enabled sessions of on-network infrastructure controls. As an IT integrated solution, DSView delivers secured web-browser enabled sessions to Virtual Machines
1	Software	DSV4.5-BASE, DSV4.5-500DEV, 1YRSLV-500DEV	DSView delivers secured web-browser enabled sessions of on-network infrastructure controls. As an IT integrated solution, DSView delivers secured web-browser enabled sessions to Virtual Machines
1	Software	ENVA-SERVER, ENVA-DEV-500, ENVA-STUP-500, ENVA-SERVER-SA, ENVA-SA-500	Vertiv™ Environet™ Alert provides industry companies with critical facility monitoring software that is affordable and easy to use. This solution delivers superior monitoring, and alerting.

\*Additional accessories and components are required and included in the integrated solution. Contact a Vertiv Partner for the complete bill of materials, to receive pricing, and to purchase.

## Recommended Upgrades

Qty	Product Summary	Model #:	Description
1	Row Based Air Cooling	CR035RA-11547620	Redundant CR035RA 600mm Wide CRV Unit with outdoor condensing unit and lee-temp kit.
1	Software	ENVA-SERVER, ENVA-DEV-500, ENVA-STUP-500, ENVA-SERVER-SA, ENVA-SA-500	Vertiv™ Environet™ Alert provides industry companies with critical facility monitoring software that is affordable and easy to use. This solution delivers superior monitoring, and alerting.

Explore all **Commercial and Office** form factors and power configurations available, **Endpoint, Rack, and Row** by visiting the **Solution Builder** on **Vertiv.com** or by contacting a **Vertiv Sales Representative**.